





SPECIFICATIONS

Rated Current:3.0AMP
Contact Resistance:20mΩ Max
Withstand Voltage:1000V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:−40°C to +105°C

Contact Material:Brass
Contact Plating:Au Or Tin Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Max.Processing Temp: 230°C for 30–60 seconds
(260°C for 10 seconds)



Ordering Information

P X X X XX X XX X XXX

产品型号	间距	塑胶材质	接触	绝缘材料	产品型号	绝缘厚度	包装方式	序列号
P=材料	1=1.27 A=1.0	1=单排	1~40P	1=DIP	00=常规	1=管接	1=管接	
	2=2.0 B=1.5	2=双排		2=RA	01=1u"	2=通接	2=通接	
	3=2.54 C=2.0	3=三排		3=PPS	02=2u"	3=通接	3=通接	
	5=1.9 D=2.5	4=四排		4=SMT	03=3u"	4=通接	4=通接	
	A=1.27*2.54			5=板贴脚	9=PA6T	5=直插		

Dimension antitheses list									
ITEM	PA	PB	PW	L1	L2	L3	H	W	
001	6.00	3.20	5.00	11.00			2.5	2.5	
Alternate									

深圳市连盛精密连接器有限公司									
		OPERATION				SCALE		FIT	
							UNIT	mm	
							SIZE	A4	
							SHEET	1/1	
							PROJ.		
							PART NO. 1010301742		
							TITLE: 2.54PH 1XNP SMT		