


RoHS




SPECIFICATIONS

Rated Current:3.0AMP
Contact Resistance:20mΩ Max
Withstand Voltage:1000V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:-40°c to +105°c

Contact Material:Brass
Contact Plating:Au Or Tin Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 10 seconds)



Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



Ordering Information

P X X X XX X XX X XXX

产品类别 间距 塑胶高度 材料 单排/双排 产品形态 塑胶材料 电镀厚度 包装方式 序列号
P=排针 I=1.27 A=1.0 1=单排 1=DIP 1=PB1 00=常规 1=管装
2=2.0 B=1.5 2=双排 2=RA 2=LCP 01=1u" 2=卷装
3=2.54 C=2.0 3=三排 3=SM 3=PPS 02=2u" 3=盒装
4=3.96 D=2.5 4=四排 4=SM 4=PA46 03=3u" 4=我装
5=1.0 A=1.27*2.54 5=PA6T 9=PA9T 5=盒装

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL	OPERATION		DRAW	SCALE		FIT	PART NO.	TITLE:
						X.X	±0.30		UNIT	mm			
A0	2012.07.02	NEW DRAWING		X.XXX	±0.10	CHECK			SIZE	A4	1/1	1010301718	2.54PH 1XNP 90度
1						Angle	±3°	APPROVE					

Dimension antitheses list									
ITEM	PA	PB	PC	L1	L2	L3	H	W	
001	6.00	4.30	3.00	13.80			2.5	2.5	
Alternate									

深圳市连盛精密连接器有限公司