

Rohs

SPECIFICATIONS

Rated Current:3.0AMP

Contact Resistance: 20mΩ Max

Withstand Voltage:1000V AC/DC

Insulation Resistance: 1000M Ω Min

Operation Temperature: -40°C to $+105^{\circ}\text{C}$

Contact Material:Brass


Contact Plating: Au or Sn Over Ni

Insulator Material: Polyester (UL94V-0)


Standard: PA6T

Max. Processing Temp: 230°C for 30–60 seconds

(260°C for 5 seconds)



Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE $\pm$ 0.05)





Ordering Information

P X X X XX X X XX X XXXX

[illegible]

						三阳去控制蛙主水 三阳去控制蛙主水
			OPERATION			
			DRAW			
			SCALE			
			FIT			

Dimension onlinetheses list								
ITEM	PA	PB	PW	L1	L2	L3	H	W
001	6.00	3.20	7.50	11.00			2.5	5.0
Alternate								



深圳市建盛精密连接器有限公司										
			X.X	±0.30				UNIT	mm	
			X.XX	±0.20	CHECK			SIZE	A4	
			X.XXX	±0.10				SHEET	1/1	
A0	2012.04.11	NEW DRAWING	Angle	±3°	APPROVE					
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL			PROJ.		
					PART NO.					1010301739
					TITLE:					2.54PH H=2.5 2XNP SMT=7.5 PAG.0 PB3.2 L=11.0 AU0.6U PA6T