

123456789

RoHS

SPECIFICATIONS

Rated Current:3.0AMP

Contact Resistance:20mΩ Max

Withstand Voltage:1000V AC/DC

Insulation Resistance:1000MΩ Min

Operation Temperature:−40℃ to +105℃


Contact Material:Brass

Contact Plating:Au or Sn Over Ni




Insulator Material:Polyester(UL94V−0)

Standard: PA6T

Max.Processing Temp: 230℃ for 30−60 seconds
(260℃ for 5 seconds)



Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



Ordering Information

P	X	X	X	XX	X	XX	X	XXXX
产品类别	间距	额定电流	接触	接触材料	绝缘材料	电绝缘材料	生产方式	序列号
P=3种	1=1.27	A=1.0	1=4种	1=PP	1=PPBT	00=无漆	1=直插	
	2=2.0	B=1.5	2=4种	2=RA	2=ICP	01=有漆	2=贴片	
	3=2.54	C=2.0	3=3种	3=SA	3=PPS	02=30°	3=贴片	
	4=3.96	D=2.5	4=4种	4=SH	4=PA46	03=90°	4=贴片	
	5=1.0			5=绝缘	5=PA6T		5=贴片	
	A=1.27	2.54						

Dimension onthseses list									
ITEM	PA	PB	PW	L1	L2	L3	H	W	
001	6.00	3.20	7.50	11.00			2.5	5.0	
Alternate									

				OPERATION								深圳市连盛精密连接器有限公司
				X.X	±0.30	DRAW						
				X.XX	±0.20	CHECK						
				X.XXX	±0.10							
				Angle	±3°	APPROVE						
				DIM	TOL							