

Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE $\pm$ 0.05)

SPECIFICATIONS

Rated Current:3.0AMP

Contact Resistance: 20m Ω Max

Withstand Voltage:1000V AC/DC

Insulation Resistance: 1000M Ω Min

Operation Temperature: -40°C to $+105^{\circ}\text{C}$

Contact Material:Brass





Contact Plating: Au Or Tin Over Ni

Insulator Material: Polyester (UL94V-0)

Standard: PA6T

Max.Processing Temp: 230°C for 30–60 seconds

(260°C for 10 seconds)



Ordering Information

P
X
X
X
XX
X
X
XX
X
XXXX

[illegible]

Dimension antitheses list								
ITEM	PA	PB	PW	L1	L2	L3	H	W
001	6,00	3,20	5,00	11,00			2,5	2,5
Alternate								

				OPERATION		DRAW			SCALE	FIT	深圳市连盛精密连接器有限公司		
				X.X	±0.30				UNIT	mm			
				X.XX	±0.20		CHECK			SIZE			A4
				X.XXX	±0.10					SHEET			1/1
A0	2012.03.28	NEW DRAWING		Angle	±3°	APPROVE			PROJ.				TITLE:
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL							2.54PH 1XNP SMT	

深圳市连盛精密连接器有限公司

PART NO.	1010301746
----------	------------

TITLE: 2.54PH 1XNP SMT