

Rohs

SPECIFICATIONS

Rated Current:3.0AMP

Contact Resistance: 20m Ω Max

Withstand Voltage:1000V AC/DC

Insulation Resistance: 1000M Ω Min

Operation Temperature: -40°C to $+105^{\circ}\text{C}$

Contact Material:Brass



Contact Plating: Au Or Tin Over Ni

Insulator Material: Polyester (UL94V-0)

Standard: PA6T



Max.Processing Temp: 230°C for 30-60 seconds

(260°C for 10 seconds)



Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE $\pm$ 0.05)

Ordering Information

[illegible]

Dimension antitheses list								
ITEM	PA	PB	PC	L1	L2	L3	H	W
001	6.00	4.30	3.00	13.80			2.5	2.5
Alternate								

深圳市连盛精密连接器有限公司										
						OPERATION		DRAW		
						X.X	±0.30			
						X.XX	±0.20			
						X.XXX	±0.10			
A0	2012.07.02	NEW DRAWING				Angle	±3°	APPROVE		
REV	DATE	MODIFICATION DESCRIPTION			CHANGE	DIM	TOL			
					SCALE	FIT				
					UNIT	mm				
					SIZE	A4				
					SHEET	1/1				
					PROJ.					
					TITLE:					
					PART NO.	1010301316				
					2.54PH 1XNP 90度					