





RoHS

SPECIFICATIONS

Rated Current: 3.0AMP
 Contact Resistance: 20mΩ Max
 Withstand Voltage: 1000V AC/DC
 Insulation Resistance: 1000MΩ Min
 Operation Temperature: -40°C to +105°C
 Contact Material: Brass
 Contact Plating: Au or Sn Over Ni
 Insulator Material: Polyester (UL94V-0)
 Standard: PA6T
 Max. Processing Temp: 230°C for 30-60 seconds
 (260°C for 5 seconds)



Ordering Information

P	X	X	X	XX	X	XX	X	XXXX
产品型号	间距	接触高度	绝缘	接触长度	产品包装	绝缘材料	电镀厚度	生产方式
1=3*4	1=1.27	A=1.0	1=4*4	1=4*4	1=DIP	1=ABS	0.05	1=直插
	2=2.0	B=1.5	2=3*3	2=3*3	2=R/A	2=PC	0.1	2=弯插
	3=2.54	C=2.0	3=3*3	3=3*3	3=SMT	3=PPS	0.2	3=直插
	4=3.96	D=2.5	4=4*4	4=4*4	4=SH	4=PA6	0.3	4=弯插
	5=1.0				5=翻盖	5=PA6T	0.5	5=直插
	A=1.27	2.54						

Dimension orithesses list									
ITEM	PA	PB	PW	L1	L2	L3	H	W	
001	6.00	3.20	7.50	11.00			2.5	5.0	
Attende									

深圳市连盛精密连接器有限公司

OPERATION		DRAW		SCALE		FIT	
X.X	±0.30			UNIT	mm		
X.XX	±0.20	CHECK		SIZE	A4		
X.XXX	±0.10	APPROVE		SHEET	1/1		
Angle	±5°			PROJ.			
DIM	TOL						
PART NO.				1010301730			
TITLE:				2.54PH H=2.5 2XNP SMT=7.5 PA6.0			
				PB3.2 L=11.0 AU0.6U PA6T			