





RoHS

Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)

SPECIFICATIONS

Rated Current:3.0AMP
Contact Resistance:20mΩ Max
Withstand Voltage:1000V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:−40°c to +105°c

Contact Material:Brass
Contact Plating:Au Or Tin Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Max.Processing Temp: 230°C for 30–60 seconds
(260°C for 10 seconds)



Ordering Information

P X X X XX X XX X XXX

产品型号	间距	塑胶材质	接触	绝缘材料	产品型号	绝缘材料	电绝缘度	包装方式	序列号
P=材料	1=1.27 A=1.0	1=双排	1~40P	1=DIP	1=FRIT	00=常规	1=常规	1=常规	
	2=2.0 B=1.5	2=双排		2=RA	2=LCP	01=1u"	2=常规	2=常规	
	3=2.54 C=2.0	3=三排		3=SMT	3=PPS	02=2u"	3=常规	3=常规	
	5=1.0	4=四排		4=SMT	4=PA46	03=3u"	4=常规	4=常规	
	A=1.27*2.54			5=板级插	5=PA6T		5=常规	5=常规	
				9=PA9T					

ITEM	PA	PB	PW	L1	L2	L3	H	W
001	6.00	3.20	5.00	11.00			2.5	2.5
Alternate								

深圳市连盛精密连接器有限公司

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL	APPROVE	PROJ.	TITLE:
A0	2012.03.28	NEW DRAWING						
1	2	3	4	5	6	7	8	9