





ROHS

SPECIFICATIONS

Rated Current:3.0AMP
 Contact Resistance:20mΩ Max
 Withstand Voltage:1000V AC/DC
 Insulation Resistance:1000MΩ Min
 Operation Temperature:-40°c to +105°c
 Contact Material:Brass
 Contact Plating:Au Or Tin Over Ni
 Insulator Material:Polyester(UL94V-0)
 Standard: PA6T
 Max.Processing Temp: 230°C for 30-60 seconds
 (260°C for 10 seconds)



Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



PC±0.25

Ordering Information

P X X X X XX X XX X XXXX

产品类别 间距 接触高度 排数 封装形式 产品形态 接触材料 电镀厚度 包装方式 序列号
 P=排针 I=1.27 A=1.0 1=单排 1~40P 1=DIP 1=PB1 00=常规 1=管装
 2=2.0 B=1.5 2=双排 1~40P 2=RA 2=LCP 01=1u" 2=卷装
 3=2.54 C=2.0 3=三排 3=SM 3=PPS 02=2u" 3=卷装
 4=3.96 D=2.5 4=四排 4=PA46 03=3u" 4=散装
 5=1.0 5=10 5=螺接脚 5=PA6T 9=PA9T 5=散装
 A=1.27*2.54

ITEM	PA	PB	PC	L1	L2	L3	H	W
001	6.00	4.30	3.00	13.80			2.5	2.5
Alternate								

深圳市连盛精密连接器有限公司

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION		DRAW	SCALE		FIT	PART NO.	TITLE:
				X.X	±0.30		UNIT	mm			
A0	2012.07.02	NEW DRAWING		X.XX	±0.20	CHECK	A4	1/1	1010301714	2.54PH 1XNP 90度	
1				Angle	±5°	APPROVE	SHEET	PROJ.			
				DIM	TOL						