

SPECIFICATIONS

Rated Current:3.0AMP

Contact Resistance: 20mΩ Max

Withstand Voltage:1000V AC/DC

Insulation Resistance: 1000M Ω Min

Operation Temperature: -40°C to $+105^{\circ}\text{C}$

Contact Material:Brass



Contact Plating: Au Or Tin Over Ni

Insulator Material: Polyester (UL94V-0)

Standard: PA6T



Max.Processing Temp: 230°C for 30–60 seconds

(260°C for 10 seconds)



Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE $\pm$ 0.05)

Ordering Information

[illegible]

Dimension antitheses list								
ITEM	PA	PB	PC	L1	L2	L3	H	W
001	6.00	4.30	3.00	13.80			2.5	2.5
Alternate								

深圳市连盛精密连接器有限公司												
		</										

三		FIT	
		mm	
A4			
T		1/1	
TITLE:			