





1		2		3		4		5		6				
VIEW A		3A		4A		4D		5B		6A		8A		
														
A	接线表	PIN	WIRE		WIRE		WIRE		WIRE		WIRE		WIRE	
		1	棕		棕		棕		棕		棕		白	
		2			白		白		白		白		棕	
		3	蓝		蓝		蓝		蓝		蓝		绿	
		4	黑		黑		黑		黑		黑		黄	
		5							灰		灰		灰	
		6									粉		粉	
		7											蓝	
8											红			
B														
C														
D														
注解：线缆尺寸公差														
50mm < L≤300mm ±5														
300mm < L≤500mm ±10														
500mm < L≤1000mm ±15														
1000mm < L≤1500mm ±20														
L > 1500mm ±30														
电缆信息														
芯数	线缆护套	UL	线规	温度范围										
3A/4A/4D/5B	PVC	UL1007	24AWG	-20℃~+80℃										
6A/8A	PVC	UL1007	26AWG	-20℃~+80℃										
GENERAL TOLERANCE (UNLESS SPECIFIED)														
X. ±0.50														
X.X ±0.30														
X.XX ±0.20														
X.XXX ±0.15														
ANGEL ±3°														
														
视 角 THIRD ANGLE														
绘图 DWN														
确认 CHK														
核准 APVD														
单位 UNIT	MM	版本 REV	A0	品名 TITLE		M8-Sxx-GCFM12-LPV-NZGJ								
尺寸 SIZE	A4	页码 SHEET	2 OF 2	品号 PART NO										
				型号 DRAWING NO										
1		2		3		4		5		6				