







标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE

Circuit 1



PCB LAYOUT

编号

尺寸 (mm)

A

B

2X1AW

5.40

2X2AW

4.20

9.60

2X3AW

8.40

13.80

2X4AW

12.60

18.00

2X5AW

16.80

22.20

2X6AW

21.00

26.40

2X7AW

25.20

30.60

2X8AW

29.40

34.80

2X9AW

33.60

39.00

2X10AW

37.80

43.20

2X11AW

42.00

47.40

2X12AW

46.20

51.60

SPECIFICATIONS

1.Current Rating: 7A AC, DC

2.Voltage Rating: 600V AC, DC

3.Temperature Range: -25°C~+85°C

4.Contact Resistance: 20mΩ Max

5.Insulation Resistance: 1000MΩ Min

6.Withstanding Voltage: 1500V AC/minute

7.Material: Wafer PA66

PIN Brass Tin-plated

2	插针	铜	镀锡	
1	底座	PA66	本色	
序号	品名	材质	电镀/颜色	备注



深圳市虹成电子有限公司

品名

TITLE

料号

PART NO

针座

HC-5557-4.2-2x8AW

GENERAL TOLERANCES
(UNLESS SPECIFIED)比列
SCALE

1:1

X.±0.25 X.±2"

单位
UNIT

MM

.X.±0.25 .X.±1"

张数
PART NO

1 OF 1

.XX±0.15 .XX±0.5"

审核
CHECKED

夏操云

.XXX±0.10 .XXX±0.5"

批准
APPROVE

赵亮亮

