









PCB Layout



说明:

- 1.产品表面清洁,无锈蚀、氧化、裂纹、缺芯、毛刺、及其它机械损伤;
- 2.塑胶材料:LCP UL94V-0,颜色:本色;
- 3.焊片:黄铜,镍底30u"Min.,镀锡50u"Min.;
- 4.接触针:黄铜,镍底30u"Min.,镀锡50u"Min.;
- 5.满足灼热丝温度850度.
- 6.工作温度-40~+85°C
- 7.额定电流:0.7A AC/DC
- 8.额定电压:30V AC/DC
- 9.接触阻抗:30mΩ Max.
- 10.绝缘阻抗:100MΩ Min.
- 11.耐压:200V AC FOR 1 MINUTE

P/N	PIN	DIM A	DIM B	DIM C	DIM D
BX-0.8-2PLT-XM	2	0.80	3.04	3.80	1.90
BX-0.8-3PLT-XM	3	1.60	3.84	4.60	2.70
BX-0.8-4PLT-XM	4	2.40	4.64	5.40	3.50
BX-0.8-5PLT-XM	5	3.20	5.44	6.20	4.30
BX-0.8-6PLT-XM	6	4.00	6.24	7.00	5.10
BX-0.8-7PLT-XM	7	4.80	7.04	7.80	5.90
BX-0.8-8PLT-XM	8	5.60	7.84	8.60	6.70
BX-0.8-9PLT-XM	9	6.40	8.64	9.40	7.50
BX-0.8-10PLT-XM	10	7.20	9.44	10.20	8.30
BX-0.8-11PLT-XM	11	8.00	10.24	11.00	9.10
BX-0.8-12PLT-XM	12	8.80	11.04	11.80	9.90
BX-0.8-13PLT-XM	13	9.60	11.84	12.60	10.70
BX-0.8-14PLT-XM	14	10.40	12.64	13.40	11.50
BX-0.8-15PLT-XM	15	11.20	13.44	14.20	12.30
BX-0.8-16PLT-XM	16	12.00	14.24	15.00	13.10
BX-0.8-17PLT-XM	17	12.80	15.04	15.80	13.90
BX-0.8-18PLT-XM	18	13.60	15.84	16.60	14.70
BX-0.8-19PLT-XM	19	14.40	16.64	17.40	15.50
BX-0.8-20PLT-XM	20	15.20	17.44	18.20	16.30

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA			料号 PART NO.	BX-0.8-NPLT-XM	版本 REV.	A		
			X.±0.30	X".:±5°					审核 CHECK	EVA	品名 TITLE	0.8-NP立贴加盖,卷装,亮锡,LCP	页次 SHEET	1/1
			.X±0.25	X.X":±3°					核准 APPROVAL	JADE	客户料号 CUTM.NO.			
			.XX±0.20	X.XX":±1°					单位 UNITS	MM	比例 SCALE	1:1	 Bossie (博锡)	