



3D View



(For Reference Only)
Stated At Compression

NOTES:

1:MATERIAL

1-1: C5210 THICKNE=0.10MM

2:SPECIFICATIONS

2-1: RATED CURRENT: 0.50A

2-2: VOLTAGE RATING: 12V

2-3: CONTACT RESISTANCE: 30MΩ/MAX

2-4: WELDING THRUST: ≥3KG

2-5: OPERATING TEMPERATURE: -40°C~+85°C

3:DURABILITY: 100 CYCLES




4:SALT SPRAY TIME: 24H

5:ELECTROPLATE: THE NICKEL-PLATED SUBSTRATE IS 60u" MIN

6:REQUIREMENTS

6-1:TERMINAL TO EAT FULL TIN,NOTPEELING,
WELDING OBVIOUS COLOR AND OTHED ADVERSE

6-2:ROHS、REACH、HF HALOGER ADVERSE OF DOMESTIC
AND INTERNATIONAL ENVIRONMNTAL REQUIREMENTS



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.' ±2' X.X' ±0.5'	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 天线弹片 L3. 50*W1. 5*H1. 40
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW-TXT351514A
UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2412301153
			SHEET NO. 1 OF 1