





序号	名称	数量
1	接触针	n
2	定位焊片	2
3	基座	1



说明:

- 1.产品表面清洁,无锈蚀、氧化、裂纹、缺芯、毛刺、及其它机械损伤;
- 2.塑胶材料:LCP UL94V-0,颜色:本色;
- 3.焊片:黄铜,镀底30u"Min.,镀锡50u"Min.;
- 4.接触针:黄铜,镀底30u"Min.,镀锡50u"Min.;
- 5.满足灼热丝温度850度.
- 6.工作温度-40~+85°C
- 7.额定电流:1A AC/DC
- 8.额定电压:125V AC/DC
- 9.接触阻抗:20mΩ Max.
- 10.绝缘阻抗:500MΩ Min.
- 11.耐电压:250V AC FOR 1 MINUTE

P/N	PIN	DIM A	DIM B	DIM C	DIM D
ZX-MX1.25-2PWT-XM	2	1.25	7.25	3.05	7.08
ZX-MX1.25-3PWT-XM	3	2.50	8.50	4.30	8.33
ZX-MX1.25-4PWT-XM	4	3.75	9.75	5.55	9.58
ZX-MX1.25-5PWT-XM	5	5.00	11.00	6.80	10.83
ZX-MX1.25-6PWT-XM	6	6.25	12.25	8.05	12.08
ZX-MX1.25-7PWT-XM	7	7.50	13.50	9.30	13.33
ZX-MX1.25-8PWT-XM	8	8.75	14.75	10.55	14.58
ZX-MX1.25-9PWT-XM	9	10.00	16.00	11.80	15.83
ZX-MX1.25-10PWT-XM	10	11.25	17.25	13.05	17.08
ZX-MX1.25-11PWT-XM	11	12.50	18.50	14.30	18.33
ZX-MX1.25-12PWT-XM	12	13.75	19.75	15.55	19.58
ZX-MX1.25-13PWT-XM	13	15.00	21.00	16.80	20.83
ZX-MX1.25-14PWT-XM	14	16.25	22.25	18.05	22.08
ZX-MX1.25-15PWT-XM	15	17.50	23.50	19.30	23.33
ZX-MX1.25-16PWT-XM	16	18.75	24.75	20.55	24.58
ZX-MX1.25-17PWT-XM	17	20.00	26.00	21.80	25.83
ZX-MX1.25-18PWT-XM	18	21.25	27.25	23.05	27.08
ZX-MX1.25-19PWT-XM	19	22.50	28.50	24.30	28.33
ZX-MX1.25-20PWT-XM	20	23.75	29.75	25.55	29.58

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	ROSE			料号 PART NO.	ZX-MX1.25-NPWT-XM	版本 REV.	A		
			.X±0.30	X.°±5°		审核 CHECK	LEO			品名 TITLE	TX-SMT-AW针座	页次 SHEET	1/1	
			.XX±0.25	X.X°±3°			核准 APPROVAL	JOHN			客户料号 CUTM.NO.			
			.XXX±0.20	X.XX°±1°				单位 UNITS	MM	比例 SCALE	1:1	兆星精密电子（深圳）有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.		