




序号	名称	数量
1	基座	1
2	阳接触针	n
3	定位焊片	2



说明:

- 1.产品表面清洁,无锈蚀、氧化、裂纹、缺芯、毛刺、及其它机械损伤;
- 2.塑胶材料:LCP UL94V-0,颜色:本色;
- 3.焊片:黄铜,镀底30u"Min.,镀锡50u"Min.;
- 4.接触针:黄铜,镀底30u"Min.,镀锡50u"Min.;
- 5.满足灼热丝温度850度.
- 6.工作温度-40~+85°C
- 7.额定电流:2A AC/DC
- 8.额定电压:100V AC/DC
- 9.接触阻抗:10mΩ Max.
- 10.绝缘阻抗:1000MΩ Min.
- 11.耐压:800V AC FOR 1 MINUTE

P/N	PIN	DIM A	DIM B	DIM C
BX-PH2.0-2PWT-XM	2	2.00	7.90	4.7000
BX-PH2.0-3PWT-XM	3	4.00	9.90	6.7000
BX-PH2.0-4PWT-XM	4	6.00	11.90	8.7000
BX-PH2.0-5PWT-XM	5	8.00	13.90	10.7000
BX-PH2.0-6PWT-XM	6	10.00	15.90	12.7000
BX-PH2.0-7PWT-XM	7	12.00	17.90	14.7000
BX-PH2.0-8PWT-XM	8	14.00	19.90	16.7000
BX-PH2.0-9PWT-XM	9	16.00	21.90	18.7000
BX-PH2.0-10PWT-XM	10	18.00	23.90	20.7000
BX-PH2.0-11PWT-XM	11	20.00	25.90	22.7000
BX-PH2.0-12PWT-XM	12	22.00	27.90	24.7000
BX-PH2.0-13PWT-XM	13	24.00	29.90	26.7000
BX-PH2.0-14PWT-XM	14	26.00	31.90	28.7000
BX-PH2.0-15PWT-XM	15	28.00	33.90	30.7000
BX-PH2.0-16PWT-XM	16	30.00	35.90	32.7000
BX-PH2.0-17PWT-XM	17	32.00	37.90	34.7000
BX-PH2.0-18PWT-XM	18	34.00	39.90	36.7000
BX-PH2.0-19PWT-XM	19	36.00	41.90	38.7000
BX-PH2.0-20PWT-XM	20	38.00	43.90	40.7000

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA			料号 PART NO.	BX-PH2.0-NPWT-XM	版本 REV.	A
			X.±0.30	X°.±5°	审核 CHECK	EVA			品名 TITLE	PH-SMT-AW针座	页次 SHEET	1/1
			.X±0.25	X.X°.±3°	核准 APPROVAL	JADE			客户料号 CUTM.NO.			
			.XX±0.20	X.XX°.±1°								
					单位 UNITS	MM	比例 SCALE	1:1	 Bossie (博锡)			