






WAFER(180°)

Part No: 3962S
 Material: pin/post Brass Tin/Gold-plated
 Wafer: Nylon 66 UL94V-0
 Circuits: 2-12circuits available
 Insulation resistance: 1000M /min
 Withstand voltage: 1500V AC/minuite
 Current rating: 7A AC/DC
 Voltage rating: 250V AC/DC

TOLERANCE TABLE	
. 0	± 0.20
. 00	± 0.15
. 000	± 0.05

APPROVED:	DATE:	C _{kmtw} 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRYCO., LTD			
CHECKED:	DATE:	TITLE: 3962S-5P 空第3PIN			
DRAWN: LYF	DATE: 2022-07-07	CLIENT P/N		W-3962S05P-0005	
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-3962-0007	REV.	A



KL00