






序号	名称	数量
1	基座	1
2	阳接触针	n
3	焊片	2

说明:

- 1.产品表面清洁,无锈蚀、氧化、裂纹、缺芯、毛刺、及其它机械损伤;
- 2.塑胶材料:LCP UL94V-0,颜色:本色;
- 3.焊片:黄铜,镀底30u"Min.,镀锡50u"Min.;
- 4.接触针:黄铜,镀底30u"Min.,镀锡50u"Min.;
- 5.满足灼热温度850度.
- 6.工作温度-40~+85°C
- 7.额定电流:2A AC/DC
- 8.额定电压:100V AC/DC
- 9.接触阻抗:10mΩ Max.
- 10.绝缘阻抗:1000MΩ Min.
- 11.耐压:800V AC FOR 1 MINUTE



PCB LAYOUT
TOL.: ±0.05

P/N	PIN	DIM A	DIM B	DIM C
ZX-HY2.0-2PWT-XM	2	2.00	8.00	4.80
ZX-HY2.0-3PWT-XM	3	4.00	10.00	6.80
ZX-HY2.0-4PWT-XM	4	6.00	12.00	8.80
ZX-HY2.0-5PWT-XM	5	8.00	14.00	10.80
ZX-HY2.0-6PWT-XM	6	10.00	16.00	12.80
ZX-HY2.0-7PWT-XM	7	12.00	18.00	14.80
ZX-HY2.0-8PWT-XM	8	14.00	20.00	16.80
ZX-HY2.0-9PWT-XM	9	16.00	22.00	18.80
ZX-HY2.0-10PWT-XM	10	18.00	24.00	20.80
ZX-HY2.0-11PWT-XM	11	20.00	26.00	22.80
ZX-HY2.0-12PWT-XM	12	22.00	28.00	24.80
ZX-HY2.0-13PWT-XM	13	24.00	30.00	26.80
ZX-HY2.0-14PWT-XM	14	26.00	32.00	28.80
ZX-HY2.0-15PWT-XM	15	28.00	34.00	30.80
ZX-HY2.0-16PWT-XM	16	30.00	36.00	32.80
ZX-HY2.0-17PWT-XM	17	32.00	38.00	34.80
ZX-HY2.0-18PWT-XM	18	34.00	40.00	36.80
ZX-HY2.0-19PWT-XM	19	36.00	42.00	38.80
ZX-HY2.0-20PWT-XM	20	38.00	44.00	40.80

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	ROSE			料号 PART NO.	ZX-HY2.0-NPWT-XM	版本 REV.	A
			.X±0.30	X.°±5°	审核 CHECK	LEO			品名 TITLE	PHB-SMT-A	页次 SHEET	1/1
			.XX±0.25	X.X°±3°	核准 APPROVAL	JOHN			客户料号 CUTM.NO.			
			.XXX±0.20	X.XX°±1°	单位 UNITS	MM	比例 SCALE	1:1	 兆星精密电子（深圳）有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.			