




Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



SPECIFICATIONS

Current Rating:3.0AMP

Contact Resistance:10mΩMax

Dielectric Strength:Min 1000V RMS

Operation Temperature:-40°C to +105°C

Contact Material:Brass

Contact Clip(4/6 finger):Becu(C17200)

Accepted Pin:Ø0.40 to 0.60mm

Insulator Material:Polyester(UL94V-0)

Standard: PPS

Soldering temperature: 260°C±5° 5S

Ordering Information

PM 200 - * - N - Z - * - ** - C

No. of Rows
1=Single Row
2=Dual Row


No. of Pins
02-40Pin

Type
2=直针
B=弯针
S=立脚
R=带脚

Length
(mm)

Contact Plating
G0:Gold Flash
G1:1u" Gold
G2:3u" Gold
G3:5u" Gold
G4:10u" Gold
G5:15u" Gold
G6:30u" Gold
S0:Gold Flash/Tin
S1:Tin

Round Pin
(圆针)

			GENEERL TOLERANCE	制 图 DRAWING		 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
			DIM TOL	审 核 CHECK					
			X.X ±0.30	批 准 APPROVAL					
			X.XX ±0.20	比 例 SCALE					
1	初版发行		X.XXX ±0.10	投 影 Projection		产品名称 TITLE	2.0 单排 排母 圆直针	版 本 REV.	A
序号 No.	变更内容 MODIFY CONTENT	日 期 MODIFY DATE	Angle ±3.0°			产品料号 PART NO.	PM200-1-N-Z-3.0-XX-C	单 位 UNITS	mm
						材 料 MATERIAL		页 次 SHEET	1/1