







SPECIFICATIONS

- 1、Current Rating: 1A AC, DC
- 2、Voltage Rating: 50V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 100MΩ Min
- 6、Withstanding Voltang: 500V AC/minute
- 7、Material: PA66,UL94V-0

编 号	尺寸 (mm)	
	A	B
A1001-02Y	1.00	5.00
A1001-03Y	2.00	6.00
A1001-04Y	3.00	7.00
A1001-05Y	4.00	8.00
A1001-06Y	5.00	9.00
A1001-07Y	6.00	10.00
A1001-08Y	7.00	11.00
A1001-09Y	8.00	12.00
A1001-10Y	9.00	13.00
A1001-11Y	10.00	14.00
A1001-12Y	11.00	15.00
A1001-20Y	19.00	23.00

制图 DRAWN	变更内容 DESCRIPTION	日 期 DATE	GENE RL TOLERANCE		制 图 Mapping	黄彬		料 号 PART NO.	HX SH1.0-7Y	版 本 REV.	A	
			X.±0.25	X.*±2°				品 名 TITLE	压线端子胶壳	页 次 SHEET	1/1	
								.X±0.20	.X*±1°	客户料号 CUTM. NO.		
			.XXX±0.10	.XXX*±0.5°	单 位 Units	MM	比 例 SCALE	1:1	 韩下 [®] 深圳市韩下电子有限公司			