

A

B

C





D

E

F

版次  
0变更摘要  
新产品发行

日期



#### 技术指标:

1. 温度范围: -25° C ~ +85° C.
2. 额定电压: 50V AC, DC.
3. 耐电压: 500V AC/minute.
4. 接触电阻: ≤ 20mΩ .
5. 绝缘电阻: ≥ 100MΩ.
6. 额定电流: 1A AC, DC.
7. 材质/阻燃等级 : PA66, UL94V-0



® 深圳市韩下电子有限公司

DRAW: 黄彬 2018-05-22

DESIGN:

CHECK: 张伟 2018-05-22

APPROVED: 罗小春 2018-05-22

TITLE:  
压线端子胶壳

SERIES: SH1.0K SERIES

P/N:

CUSTOMER DRAWING

REV. 1.00 SCALE N/A

CKT	A	B	C
2	1.00	2.40	5.0
3	2.00	3.40	6.0
4	3.00	4.40	7.0
5	4.00	5.40	8.0
6	5.00	6.40	9.0
7	6.00	7.40	10.0
8	7.00	8.40	11.0
9	8.00	9.40	12.0
10	9.00	10.40	13.0
11	10.00	11.40	14.0
12	11.00	12.40	15.0
13	12.00	13.40	16.0
14	13.00	14.40	17.0
15	14.00	15.40	18.0
16	15.00	16.40	19.0
18	17.00	18.40	21.0
20	19.00	20.40	23.0

DRAW NAME:  
HX SHG1.0-8Y

DRAW NO.

UNIT: mm SHEET: 1/1

A

B

C

D

E

F