








2~3 Pin结构外形(锁扣)

CKT	A	B	C
2	1.25	2.72	5.70
3	2.50	3.97	6.95
4	3.75	5.22	8.20
5	5.00	6.47	9.45
6	6.25	7.72	10.70
7	7.50	8.97	11.95
8	8.75	10.22	13.20
9	10.00	11.47	14.45
10	11.25	12.72	15.70
11	12.50	13.97	16.95
12	13.75	15.22	18.20
13	15.00	16.47	19.45
14	16.25	17.72	20.70
15	17.50	18.97	21.95
16	18.75	20.22	23.20
18	21.25	22.72	25.70
20	23.75	25.22	28.20

- 技术指标:
1. 温度范围: $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
 2. 额定电压: 125V AC, DC.
 3. 耐电压: 250V AC/minute.
 4. 接触电阻: $\leq 20\text{m}\Omega$.
 5. 绝缘电阻: $\geq 100\text{M}\Omega$.
 6. 额定电流: 1A AC, DC.
 7. 材质/阻燃等级: PA66/UL94V-0



一般公差 (TOLERANCE)
X. ± 0.50 .XX ± 0.10
.X ± 0.20 .XXX ± 0.05
ANGLES $\pm 1^{\circ}$

韩下 HANXIA 深圳市韩下电子有限公司

品名 (TITLE)	压线端子胶壳	制图 (DR)	黄彬
料号 (DWG.NO)	HX MX1.25-4Y-WRS	校对 (CHKD)	张伟
比例 (SCALE)	1:1	审核 (APPD)	罗小春
单位 (UNITS)	mm	张数 (SHEET)	1 OF 1
		SIZE	A4
		REV	A