








3D View



(1.30)WORKING HEIGHT

RECOMMENDED PCB LAYOUT
TOLERANCE±0.05(焊盘推荐图)METAL MASK T=0.10
TOLERANCE±0.05(钢网推荐图)

NOTES

(1) MATERIAL: SUS-301 THICKNESS=0.10mm

(2) PRODUCT SPECIFICATIONS:

2-1: RATED CURRENT: 1.0A

2-2: VOLTAGE RATING: 1.50V

2-3: CONTACT RESISTANCE: 80mΩ/MAX

2-4: WELDING THRUST: ≥3KG

2-5: OPERATING TEMPERATURE: -40°C~+85°C

2-6: DURABILITY: 1500 CYCLES

(3): SALT SPRAY: 24 HOURS

(4): REQUIREMENTS

4-1: TERMINAL TO EAT FULL TIN, NOT PEELING

WELDING OBVIOUS COLOR AND OTHER ADVERSE

4-2: ROHS, REACH, HF HALOGEN ADVERSE OF DOMESTIC
AND INTERNATIONAL ENVIRONMENTAL REQUIREMENTS

深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X" ±0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 天线弹片 L2.50*W1.00*H1.80	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW-TXT251018A	
 UNIT: mm [inch] SCALE: 1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2412301428	
			SHEET NO. 1 OF 1	