




REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A			2025.06.06	
A2	N/A			2025.08.26	



SPECIFICATION

Contact Rating 50mA,12V DC
Contact Resistance 100mΩ max
Insulation Resistance 100MΩ min.100V DC
Dielectric Strength 250V AC/1minute
Travel 0.13±0.05mm
Operating Temp -40 ~+85
Operating Life: 500 000cycles

PAPT NO	TS-2030-X
Operating Force	B:160gf C:260gf
Height	H:0.58

5	Knob	1	PA9T	Black
4	Film	1	PA9T	White
3	Dome	3	SUS 301	Ag Over Nicke
2	Housing	1	PA9T	Black
1	Terminal	2	Phosphor bronze	Ag Over Nicke
ITEM	PAPT NAME	QTY	MATERIAL	FINISHING

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN		VIEW:	MODEL TYPE: TACT SWITCH
CHECKED		UNIT: mm/in	PART NO.: TS-2030-X
APPROVED		SIZE: A4	DWG NO.: