

标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE

编号

尺寸 (mm)

A

B

2X1A

4.20

5.40

2X2A

8.40

9.60

2X3A

12.60

13.80

2X4A

16.80

22.20

2X5A

21.00

26.40

2X6A

25.20

30.60

2X7A

29.40

34.80

2X8A

33.60

39.00

2X9A

37.80

43.20

2X10A





42.00

47.40



2X11A

46.20

51.60



2x1A



PCB LAYOUT

SPECIFICATIONS

1.Current Rating: 7A AC, DC

2.Voltage Rating: 600V AC, DC

3.Temperature Range: -25°C~+85°C

4.Contact Resistance: 20mΩ Max

5.Insulation Resistance: 1000MΩ Min

6.Withstanding Voltage: 1500V AC/minute

7.Material: Wafer PA66

PIN Brass Tin-plated

2	插针	铜	镀锡	
1	底座	PA66	本色	
序号	品名	材质	电镀/颜色	备注




深圳市虹成电子有限公司

品名 TITLE	针座
料号 PART NO	HC-5557-4. 2-2x6A

GENERAL TOLERANCES
(UNLESS SPECIFIED)比 例
SCALE

1:1



X±0.25

X*±2°

单位
UNIT

MM

制图
DRAW

AhYe

.X±0.25

.X*±1°

张 数
PART NO

1 OF 1

审 核
CHECKED

夏操云

.XX±0.15

.XX*±0.5°

版 本
REV

A

批 准
APPROVE

赵亮亮

.XXX±0.10

.XXX*±0.5°

