




REV.	EC#	DESCRIPTION	DATE	DRAWN	CHECK	APPROVED
1.00		初版发行	2020-05-22			

1.0卧式贴片	A-(mm)	B-(mm)	C-(mm)
1.0-2PWT	1.00mm	3.50mm	4.30mm
1.0-3PWT	2.00mm	4.50mm	5.30mm
1.0-4PWT	3.00mm	5.50mm	6.30mm
1.0-5PWT	4.00mm	6.50mm	7.30mm
1.0-6PWT	5.00mm	7.50mm	8.30mm
1.0-7PWT	6.00mm	8.50mm	9.30mm
1.0-8PWT	7.00mm	9.50mm	10.30mm
1.0-9PWT	8.00mm	10.50mm	11.30mm
1.0-10PWT	9.00mm	11.50mm	12.30mm
1.0-11PWT	10.00mm	12.50mm	13.30mm
1.0-12PWT	11.00mm	13.50mm	14.30mm
1.0-13PWT	12.00mm	14.50mm	15.30mm
1.0-14PWT	13.00mm	15.50mm	16.30mm
1.0-15PWT	14.00mm	16.50mm	17.30mm
1.0-16PWT	15.00mm	17.50mm	18.30mm
1.0-17PWT	16.00mm	18.50mm	19.30mm
1.0-18PWT	17.00mm	19.50mm	20.30mm
1.0-19PWT	18.00mm	20.50mm	21.30mm
1.0-20PWT	19.00mm	21.50mm	22.30mm

PCB LAYOUT

技术要求:

- 1) 材质:见附表;
- 2) 电镀:见附表;
- 3) 塑件表面平整、光洁、无毛刺、气泡、烧焦、变形、浇口无拉伤、多料或缺料等不良现象;
- 4) 端子表面无氧化、电镀无不良现象。

适应基板厚度: 1.2mm~1.6mm
温度范围: -25℃~85℃
额定电压: 50V AC/DC
额定电流: 1A
接触电阻: ≤0.02 Ω
绝缘电阻: ≥100M Ω
耐 压: 500V AC/minute

3	FITTING NAIL	2 PCS	材质:磷青铜,电镀:镀亮锡60u"MIN
2	PIN	n PCS	材质:磷青铜,电镀:镀亮锡60u"MIN
1	Housing	1 PCS	材质:LCP (UL94V-0),颜色:本色或黑色
NO.	NAME	Q'TY	DESCRIPTION



深圳市韩下电子有限公司

DRAW :	黄彬	2020-05-22	TITLE:	针座	DRAW NAME:
DESIGN:			SERIES:	SH1.0 SERIES	HX 1.0-4P WT
CHECK:	张伟	2020-05-22	P/N:		DRAW NO.
APPROVED	罗小春	2020-05-22	REV. 1.00	SCALE N/A	UNIT: mm
CUSTOMER DRAWING			SHEET: 1/1		

GENERAL TOLERANCES			
DIM	TOL	DIM	DEG
X.		X°.	±3.00°
X.X	±0.35	X.X°	±2.00°
X.XX	±0.25	X.XX°	±1.00°
X.XXX	±0.15	X.XXX°	