





1		2		3		4		5		6				
VIEW A		3A		4A		4D		5B		6A		8A		
														
A	接线表	PIN	WIRE		WIRE		WIRE		WIRE		WIRE		WIRE	
		1	棕		棕		棕		棕		棕		白	
		2			白		白		白		白		棕	
		3	蓝		蓝		蓝		蓝		蓝		绿	
		4	黑		黑		黑		黑		黑		黄	
		5							灰		灰		灰	
		6									粉		粉	
		7											蓝	
	8											红		
B														
C														
D														
注解：线缆尺寸公差														
50mm < L ≤ 300mm ±5														
300mm < L ≤ 500mm ±10														
500mm < L ≤ 1000mm ±15														
1000mm < L ≤ 1500mm ±20														
L > 1500mm ±30														
电缆信息														
芯数		线缆护套	UL	线规	温度范围									
3A/4A/4D/5B		PVC	UL1007	24AWG	-20℃~+80℃									
6A/8A		PVC	UL1007	26AWG	-20℃~+80℃									
GENERAL TOLERANCE (UNLESS SPECIFIED)														
X. ±0.50														
X.X ±0.30														
X.XX ±0.20														
X.XXX ±0.15														
ANGEL ±3°														
														
视 角 THIRD ANGLE														
绘图 DWN		确认 CHK		核准 APVD		单位 UNIT		MM	版本 REV	A0	品名 TITLE		M8-Pxx-GCFM8-LPV-NZGJ	
尺寸 SIZE		A4	页码 SHEET	2 OF 2	型号 DRAWING NO									
CASN® 正成														