







标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE

Circuit 1



PCB LAYOUT

编号

尺寸 (mm)

A

B

2X1AW

5.40

2X2AW

9.60

2X3AW

13.80

2X4AW

18.00

2X5AW

22.20

2X6AW

26.40

2X7AW

30.60

2X8AW

34.80

2X9AW

39.00

2X10AW

43.20

2X11AW

47.40

2X12AW

51.60

SPECIFICATIONS

1.Current Rating: 7A AC, DC

2.Voltage Rating: 600V AC, DC

3.Temperature Range: -25°C~+85°C

4.Contact Resistance: 20mΩ Max

5.Insulation Resistance: 1000MΩ Min

6.Withstanding Voltage: 1500V AC/minute

7.Material: Wafer PA66

PIN Brass Tin-plated

2	插针	铜	镀锡	
1	底座	PA66	本色	
序号	品名	材质	电镀/颜色	备注



深圳市虹成电子有限公司

品名

TITLE

料号

PART NO

针座

HC-5557-4.2-2x3AW

GENERAL TOLERANCES
(UNLESS SPECIFIED)比列
SCALE

1:1

X.±0.25 X.±2"

单位
UNIT

MM

.X.±0.25 .X.±1"

张数
PART NO

1 OF 1

.XX±0.15 .XX±0.5"

审核
CHECKED

夏操云

.XXX±0.10 .XXX±0.5"

批准
APPROVE

赵亮亮

