






REV	ECN NO.	APPD
A	HC250015	PRIOJDM




电路图
SCHEMATEC



规格 Specifications

额定负荷 Rating	DC 12V/50mA
接触电阻Contact Resistance	100mΩ max.
绝缘电阻Insulation resistance	DC100V 60S 100MΩ min.
抗电强度Dielectric strength	AC250V(50~60HZ) 60S min.
操作力Operation force	250±50gf
寿命试验Operating Life	100,000 cycles
行程Travels	0.2±0.1mm



印制线路板开孔
P.C.B. HOLE DETAIL

PRODUCT NO. : 1TS022G***-***-***0CP-CT

轻触开关	编带
4.5X3.5系列	非编带, 不启用
外形:	
按钮颜色:	材料:
底座颜色:	0=初始材料
盖板颜色:	1=新增材料
↓ 初始颜色, 则不启用	依次增加
操作力度:	产品高度(H):
160=160gf	350=3.5mm
260=260gf	400=4.0mm
	500=5.0mm
	600=6.0mm
	手感:
	0=常规

6	TERMINAL	1	磷铜 0.2	Ag-PLATED
5	HOUSING	1	LCP	BLACK
4	DOME	2	SUS301 0.3	Ag-PLATED
3	FILM	1	PI	YELLOW
2	COVER	1	磷铜 0.2	Ag-PLATED
1	ACTUATOR	1	LCP/PPA	WHITE
ITEM	PART NAME	QUANTITY	MATERIAL	FINISH

>0.5°2	±0.1	UNITS MM	NAME(INTENDED USE) 4.5X3.5 TACT SWITCH	HON YUAN HON YUAN PRECISION IND. CO.,LTD. GUANGDONG, CHINA.			
>2°5	±0.25			MAT'L	PART NO.(INTENDED USE) 1TS022G-2500-3500CP-CT	TITLE: PRODUCT DRAWING	
>5°10	±0.3	FINISH	APPD: W.P.Lu 2024.10.15			DWG NO.: 1TS022G-2500-3500CP-CT	
角度	±0.5°			Q'TY	CHKD: S.L.Li 2024.10.15		SCALE
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF HON YUAN PRECISION IND. CO., LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF HON YUAN PRECISION IND. CO., LTD.			DR: C.Li 2024.10.15				10/1