





REV.		EC#	DESCRIPTION	DATE	DRAWN	CHECK	APPROVED
1.00			行发版初	2018-05-22			



16	12.00	13.00	13.50	15.60
15	11.20	12.20	12.70	14.80
14	10.40	11.40	11.90	14.00
13	9.60	10.60	11.10	13.20
12	8.80	9.80	10.30	12.40
11	8.00	9.00	9.50	11.60
10	7.20	8.20	8.70	10.80
9	6.40	7.40	7.90	10.00
8	5.60	6.60	7.10	9.20
7	4.80	5.80	6.30	8.40
6	4.00	5.00	5.50	7.60
5	3.20	4.20	4.70	6.80
4	2.40	3.40	3.90	6.00
3	1.60	2.60	3.10	5.20
2	0.80	1.80	2.30	4.40
Pin	DIM.A	DIM.B	DIM.C	DIM.D



技术要求:

- 1) 材质/阻燃等级: LCP/UL94V-0;
- 2) 塑件表面平整、光洁、无毛刺、气泡、烧焦、变形、浇口无拉伤、多料或缺料等不良现象;

温度范围: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.

额定电压: 30V, AC/DC.

耐电压: 200V, AC/minute.

接触电阻: 初期 $\leq 0.02\Omega$, 环境实验后 $\leq 0.04\Omega$.

绝缘电阻: $\geq 100\Omega$.

额定电流: 0.5A AC/DC.



深圳市韩下电子有限公司

DRAW :	黄彬	2018-05-22	TITLE: 压线端子胶壳		DRAW NAME: HX 0.8-6Y	
DESIGN:			SERIES: 0.8 SERIES		DRAW NO.	
CHECK:	张伟	2018-05-22	P/N:		UNIT: mm	SHEET: 1/1
APPROVED	罗小春	2018-05-22	REV. 1.00		SCALE	N/A
CUSTOMER DRAWING			REV. 1.00		SCALE	N/A