

A






B

C

D

E

F

版次
0变更摘要
新产品发行日期
2021/7/10

CKT	A	B	C
2	1.25	2.72	5.70
3	2.50	3.97	6.95
4	3.75	5.22	8.20
5	5.00	6.47	9.45
6	6.25	7.72	10.70
7	7.50	8.97	11.95
8	8.75	10.22	13.20
9	10.00	11.47	14.45
10	11.25	12.72	15.70
11	12.50	13.97	16.95
12	13.75	15.22	18.20
13	15.00	16.47	19.45
14	16.25	17.72	20.70
15	17.50	18.97	21.95
16	18.75	20.22	23.20
18	21.25	22.72	25.70
20	23.75	25.22	28.20

技术指标:

- 温度范围: -25° C ~ +85° C.
- 额定电压: 125V AC, DC.
- 耐电压: 250V AC/minute.
- 接触电阻: ≤ 20mΩ .
- 绝缘电阻: ≥ 100MΩ .
- 额定电流: 1A AC, DC.
- 材质/阻燃等级 : PA66/UL94V-0

2~3 Pin结构外形(锁扣)

RoHS

一般公差 (TOLERANCE)
X. ±.50 XX. ±.10
X. ±.20 XXX. ±.05
ANGLES. ±1°

深圳市韩下电子有限公司

品名 (TITLE)	压线端子胶壳		制图 (DR)	黄彬
校对 (CHKD)			张伟	
料号 (DWG.NO)	HX MX1.25-3Y-WRS		审核 (APPD)	罗小春
比例 (SCALE)	1:1		张数 (SHEET)	1 OF 1
单位 (UNITS)	mm	SIZE REV	A4	A