





版次	变更摘要	日期
0	新产品发行	



技术指标:

1. 温度范围: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$.
2. 额定电压: 50V AC, DC.
3. 耐电压: 500V AC/minute.
4. 接触电阻: $\leq 20\text{m}\Omega$.
5. 绝缘电阻: $\geq 100\text{M}\Omega$.
6. 额定电流: 1A AC, DC.
7. 材质/阻燃等级: PA66, UL94V-0

CKT	A	B	C
2	1.00	2.40	5.0
3	2.00	3.40	6.0
4	3.00	4.40	7.0
5	4.00	5.40	8.0
6	5.00	6.40	9.0
7	6.00	7.40	10.0
8	7.00	8.40	11.0
9	8.00	9.40	12.0
10	9.00	10.40	13.0
11	10.00	11.40	14.0
12	11.00	12.40	15.0
13	12.00	13.40	16.0
14	13.00	14.40	17.0
15	14.00	15.40	18.0
16	15.00	16.40	19.0
18	17.00	18.40	21.0
20	19.00	20.40	23.0

深圳市韩下电子有限公司			
DRAW:	黄彬	2018-05-22	TITLE: 压线端子胶壳
DESIGN:			DRAW NAME: HX SHG1.0-10Y
CHECK:	张伟	2018-05-22	SERIES: SH1.0K SERIES
APPROVED:	罗小春	2018-05-22	P/N:
CUSTOMER DRAWING			REV. 1.00 SCALE N/A
DRAW NO.		UNIT: mm	SHEET: 1/1