










RECOMMENDER PCB LAYOUT
TOLERANCE UNLESS OTHERWISE IS ± 0.05



Notes:

- 1.All Dimensions are in Millimeters.
- 2.Operation voltage: 10 VAC max.
- 3.Current rating : 1 Amps max.
- 4.Contact resistance: 100m ohms max.
- 5.Insulation resistance: 1000M ohms min. 500 VDC
- 6.Dielectric withstanding voltage: 500 VAC / 1minute
- 7.Operating Temperature: -20°C to $+60^{\circ}\text{C}$
- 8.Storage Temperature: -40°C to $+70^{\circ}\text{C}$
- 9.Durability 10000 cycles.



深圳市华宇创精密电子有限公司

TOLERANCE: XX ± 0.30 X.XX ± 0.25 X.XXX ± 0.15 X° $\pm 2^{\circ}$ X.X° $\pm 0.5^{\circ}$	DRAWN BY :	DATE :	PART NAME:
	陈一鸣	2014-02-23	SD 7.0 NO PUSH 短体SMT 板下型3.2H
UNIT: mm [inch] SCALE:1:1 SIZE: A4	CHECKED BY:	DATE :	PART NO.
	马跃	2014-02-23	HYCW90-SD21-325B
	APPROVED BY:	DATE :	DRAW NO:
	邱敏	2014-02-23	HYC-2502182115
			SHEET NO. 1 OF 1