




1 2 3 4 5 6 7 8 9



SPECIFICATIONS

1. Current Rating: 1A AC, DC
2. Voltage Rating: 50V AC, DC
3. Temperatuer Range: -25°C~+85°C
4. Contact Resistance: 20mΩ Max
5. Insulation Resistance: 100MΩ Min
6. Withstanding Voltang: 500V AC/minute
7. Material: PA66, UL94V-0

编 号	尺寸 (mm)	
	A	B
A1001-02Y	1.00	5.00
A1001-03Y	2.00	6.00
A1001-04Y	3.00	7.00
A1001-05Y	4.00	8.00
A1001-06Y	5.00	9.00
A1001-07Y	6.00	10.00
A1001-08Y	7.00	11.00
A1001-09Y	8.00	12.00
A1001-10Y	9.00	13.00
A1001-11Y	10.00	14.00
A1001-12Y	11.00	15.00
A1001-20Y	19.00	23.00

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 Mapping	黄彬	料号 PART NO.	SH1.0-9Y	版本 REV.	A
			X.±0.25	X.±2°						
			X.±0.20	X.±1°	审核 Audit	张伟	品名 TITLE	压线端子胶壳	页次 SHEET	1/1
			XX±0.15	XX±0.5°	核 准 Approved	罗小春	客户料号 CUTM. NO.			
			XXX±0.10	XXX±0.5°	单 位 Units	MM	比 例 SCALE	1:1		