





说明:

1. 产品表面清洁, 无锈蚀、氧化、裂纹、缺芯、毛刺、及其它机械损伤;
2. 塑胶材料: LCP UL94V-0, 颜色: 本色;
3. 焊片: 黄铜, 镍底30u"Min., 镀锡50u"Min.;
4. 接触针: 黄铜, 镍底30u"Min., 镀锡50u"Min.;
5. 满足灼热丝温度850度.
6. 工作温度-40~+85°C
7. 额定电流: 3A AC/DC
8. 额定电压: 250V AC/DC
9. 接触阻抗: 10mΩ Max.
10. 绝缘阻抗: 1000MΩ Min.
11. 耐电压: 1000V AC FOR 1 MINUTE

P/N	PIN	DIM A	DIM B	DIM C
HA2.54-2PWT	2	2.50	9.90	5.90
HA2.54-3PWT	3	5.00	12.40	8.40
HA2.54-4PWT	4	7.50	14.90	10.90
HA2.54-5PWT	5	10.00	17.40	13.40
HA2.54-6PWT	6	12.50	19.90	15.90
HA2.54-7PWT	7	15.00	22.40	18.40
HA2.54-8PWT	8	17.50	24.90	20.90
HA2.54-9PWT	9	20.00	27.40	23.40
HA2.54-10PWT	10	22.50	29.90	25.90
HA2.54-11PWT	11	25.00	32.40	28.40
HA2.54-12PWT	12	27.50	34.90	30.90
HA2.54-13PWT	13	30.00	37.40	33.40
HA2.54-14PWT	14	32.50	39.90	35.90
HA2.54-15PWT	15	35.00	42.40	38.40
HA2.54-16PWT	16	37.50	44.90	40.90
HA2.54-17PWT	17	40.00	47.40	43.40
HA2.54-18PWT	18	42.50	49.90	45.90
HA2.54-19PWT	19	45.00	52.40	48.40
HA2.54-20PWT	20	47.50	54.90	50.90

PCB LAYOUT
TOL.: ±0.05

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co., Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: HA-SMT-AW带扣针座	
DECIMALS:		PAR	HA2.54-XPWT
X.:±0.30		DWN	Lucas
X.X:±0.25		CHKD	Ethan
X.XX:±0.20		APVD	Jacob
ANGLES:		SCALE:1:1	UNIT:MM
X.X':±5°		SIZE:A4	SHEET:1F1
X.X'':±3°		CUSTOMER COPY	REV:A
X.XX':±1°			