





说明:

- 1.产品表面清洁,无锈蚀、氧化、裂纹、缺芯、毛刺、及其它机械损伤;
- 2.塑胶材料:LCP UL94V-0,颜色:本色;
- 3.焊片:黄铜,镍底30u"Min.,镀锡50u"Min.;
- 4.接触针:黄铜,镍底30u"Min.,镀锡50u"Min.;
- 5.满足灼热丝温度850度.
- 6.工作温度-40~+85°C
- 7.额定电流:2A AC/DC
- 8.额定电压:100V AC/DC
- 9.接触阻抗:10mΩ Max.
- 10.绝缘阻抗:1000MΩ Min.
- 11.耐电压:800V AC FOR 1 MINUTE



P/N	PIN	DIM A	DIM B	DIM C
PH2.0-2PWT	2	2.00	7.90	4.70
PH2.0-3PWT	3	4.00	9.90	6.70
PH2.0-4PWT	4	6.00	11.90	8.70
PH2.0-5PWT	5	8.00	13.90	10.70
PH2.0-6PWT	6	10.00	15.90	12.70
PH2.0-7PWT	7	12.00	17.90	14.70
PH2.0-8PWT	8	14.00	19.90	16.70
PH2.0-9PWT	9	16.00	21.90	18.70
PH2.0-10PWT	10	18.00	23.90	20.70
PH2.0-11PWT	11	20.00	25.90	22.70
PH2.0-12PWT	12	22.00	27.90	24.70
PH2.0-13PWT	13	24.00	29.90	26.70
PH2.0-14PWT	14	26.00	31.90	28.70
PH2.0-15PWT	15	28.00	33.90	30.70
PH2.0-16PWT	16	30.00	35.90	32.70
PH2.0-17PWT	17	32.00	37.90	34.70
PH2.0-18PWT	18	34.00	39.90	36.70
PH2.0-19PWT	19	36.00	41.90	38.70
PH2.0-20PWT	20	38.00	43.90	40.70



序号	名称	数量
1	基座	1
2	阳接触针	n
3	定位焊片	2

MANUFACTURE DWG

东莞市讯普电子科技有限公司
DongGuan XunPu Electronics Co.,LtdUNLESS OTHERWISE
SPECIFIED TOLERANCES

TITLE:

PH-SMT-AW射座

PAR

PH2.0-XPWT

DECIMALS:

ANGLES:

X.:±0.30

X':±5°

X.X:±0.25

X.X':±3°

X.XX:±0.20

X.XX':±1°

DWN

Lucas

CHKD

Ethan

APVD

Jacob

SCALE:1:1

UNIT:MM

SIZE:A4

SHEET:1F1

REV:A

CUSTOMER COPY