









P/N	PIN	DIM A	DIM B	DIM C
GH1.25-2PWT	2	1.25	3.85	5.75
GH1.25-3PWT	3	2.50	5.10	7.00
GH1.25-4PWT	4	3.75	6.35	8.25
GH1.25-5PWT	5	5.00	7.60	9.50
GH1.25-6PWT	6	6.25	8.85	10.75
GH1.25-7PWT	7	7.50	10.10	12.00
GH1.25-8PWT	8	8.75	11.35	13.25
GH1.25-9PWT	9	10.00	12.60	14.50
GH1.25-10PWT	10	11.25	13.85	15.75
GH1.25-11PWT	11	12.50	15.10	17.00
GH1.25-12PWT	12	13.75	16.35	18.25
GH1.25-13PWT	13	15.00	17.60	19.50
GH1.25-14PWT	14	16.25	18.85	20.75
GH1.25-15PWT	15	17.50	20.10	22.00
GH1.25-16PWT	16	18.75	21.35	23.25
GH1.25-17PWT	17	20.00	22.60	24.50
GH1.25-18PWT	18	21.25	23.85	25.75
GH1.25-19PWT	19	22.50	25.10	27.00
GH1.25-20PWT	20	23.75	26.35	28.25



说明:

- 1.产品表面清洁,无锈蚀、氧化、裂纹、缺芯、毛刺、及其它机械损伤;
- 2.塑胶材料:LCP UL94V-0,颜色:本色;
- 3.焊片:黄铜,镍底30u"Min.,镀锡50u"Min.;
- 4.接触针:黄铜,镍底30u"Min.,镀锡50u"Min.;
- 5.满足灼热丝温度850度.
- 6.工作温度-40~+85°C
- 7.额定电流:1A AC/DC
- 8.额定电压:50V AC/DC
- 9.接触阻抗:20mΩ Max.
- 10.绝缘阻抗:100MΩ Min.
- 11.耐电压:500V AC FOR 1 MINUTE

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: GH-SMT-AW针座	
DECIMALS:	ANGLES:	PAR	GH1.25-XPWT
X.:±0.30	X':±5°	DWN	Lucas
X.X:±0.25	X.X':±3°	CHKD	Ethan
X.XX:±0.20	X.XX':±1°	APVD	Jacob
CUSTOMER COPY		SCALE:1:1	UNIT:MM
		SIZE:A4	SHEET:1F1
			REV:A



MANUFACTURE DWG			TITLE: GH-SMT-AW针座	
UNLESS OTHERWISE SPECIFIED TOLERANCES			PAR	GH1.25-XPWT
DECIMALS:	ANGLES:		DWN	Lucas
X.:±0.30	X.':±5°		CHKD	Ethan
X.X:±0.25	X.X':±3°		APVD	Jacob
X.XX:±0.20	X.XX':±1°	CUSTOMER COPY	SCALE1:1	UNIT:MM
			SIZE:A4	SHEET:1F1
				REV:A