







## 说明:

- 1.产品表面清洁,无锈蚀、氧化、裂纹、缺芯、毛刺、及其它机械损伤;
- 2.塑胶材料:LCP UL94V-0,颜色:本色;
- 3.焊片:黄铜,镍底30u"Min.,镀锡50u"Min.;
- 4.接触针:黄铜,镍底30u"Min.,镀锡50u"Min.;
- 5.满足灼热丝温度850度.
- 6.工作温度-40~+85°C
- 7.额定电流:3A AC/DC
- 8.额定电压:250V AC/DC
- 9.接触阻抗:10mΩ Max.
- 10.绝缘阻抗:1000MΩ Min.
- 11.耐电压:1000V AC FOR 1 MINUTE

| 序号 | 名称   | 数量 |
|----|------|----|
| 1  | 基座   | 1  |
| 2  | 阳接触针 | n  |
| 3  | 焊片   | 2  |



| P/N          | PIN | DIM A | DIM B | DIM C |
|--------------|-----|-------|-------|-------|
| HA2.54-2PLT  | 2   | 2.50  | 9.90  | 5.90  |
| HA2.54-3PLT  | 3   | 5.00  | 12.40 | 8.40  |
| HA2.54-4PLT  | 4   | 7.50  | 14.90 | 10.90 |
| HA2.54-5PLT  | 5   | 10.00 | 17.40 | 13.40 |
| HA2.54-6PLT  | 6   | 12.50 | 19.90 | 15.90 |
| HA2.54-7PLT  | 7   | 15.00 | 22.40 | 18.40 |
| HA2.54-8PLT  | 8   | 17.50 | 24.90 | 20.90 |
| HA2.54-9PLT  | 9   | 20.00 | 27.40 | 23.40 |
| HA2.54-10PLT | 10  | 22.50 | 29.90 | 25.90 |
| HA2.54-11PLT | 11  | 25.00 | 32.40 | 28.40 |
| HA2.54-12PLT | 12  | 27.50 | 34.90 | 30.90 |
| HA2.54-13PLT | 13  | 30.00 | 37.40 | 33.40 |
| HA2.54-14PLT | 14  | 32.50 | 39.90 | 35.90 |
| HA2.54-15PLT | 15  | 35.00 | 42.40 | 38.40 |
| HA2.54-16PLT | 16  | 37.50 | 44.90 | 40.90 |
| HA2.54-17PLT | 17  | 40.00 | 47.40 | 43.40 |
| HA2.54-18PLT | 18  | 42.50 | 49.90 | 45.90 |
| HA2.54-19PLT | 19  | 45.00 | 52.40 | 48.40 |
| HA2.54-20PLT | 20  | 47.50 | 54.90 | 50.90 |



PCB LAYOUT

TOL.: ±0.05

|                                       |           |                                                                                                                                            |             |
|---------------------------------------|-----------|--------------------------------------------------------------------------------------------------------------------------------------------|-------------|
| MANUFACTURE DWG                       |           |  东莞市讯普电子科技有限公司<br>DongGuan XunPu Electronics Co., Ltd |             |
| UNLESS OTHERWISE SPECIFIED TOLERANCES |           | TITLE:<br>HA-SMT-A带扣针座                                                                                                                     |             |
| DECIMALS:                             | ANGLES:   | PAR                                                                                                                                        | HA2.54-XPLT |
| X.:±0.30                              | X':±5°    | DWN                                                                                                                                        | Lucas       |
| X.X:±0.25                             | X.X':±3°  | CHKD                                                                                                                                       | Ethan       |
| X.XX:±0.20                            | X.XX':±1° | APVD                                                                                                                                       | Jacob       |
| CUSTOMER COPY                         |           | SCALE:1:1                                                                                                                                  | UNIT:MM     |
|                                       |           | SIZE:A4                                                                                                                                    | SHEET:1F1   |
|                                       |           |                                                                                                                                            | REV:A       |