

说明:

1.产品表面清洁,无锈蚀、氧化、裂纹、缺芯、毛刺、及其它机械损伤;

2.塑胶材料:LCP UL94V-0,颜色:本色;

3.焊片:黄铜,镍底30u"Min.,镀锡50u"Min.;

4.接触针:黄铜,镍底30u"Min.,镀锡50u"Min.;

5.满足灼热丝温度850度.

6.工作温度-40~+85°C




7.额定电流:1A AC/DC

8.额定电压:50V AC/DC


9.接触阻抗:10mΩ Max.

10.绝缘阻抗:1000MΩ Min.

11.耐压:1000V AC FOR 1 MINUTE



P/N	PIN	DIM A	DIM B	DIM C
ZH1.5-2PWT	2	1.50	6.00	3.60
ZH1.5-3PWT	3	3.00	7.50	5.10
ZH1.5-4PWT	4	4.50	9.00	6.60
ZH1.5-5PWT	5	6.00	10.50	8.10
ZH1.5-6PWT	6	7.50	12.00	9.60
ZH1.5-7PWT	7	9.00	13.50	11.10
ZH1.5-8PWT	8	10.50	15.00	12.60
ZH1.5-9PWT	9	12.00	16.50	14.10
ZH1.5-10PWT	10	13.50	18.00	15.60
ZH1.5-11PWT	11	14.00	19.50	17.10
ZH1.5-12PWT	12	16.50	21.00	18.60
ZH1.5-13PWT	13	18.00	22.50	20.10
ZH1.5-14PWT	14	19.50	24.00	21.60
ZH1.5-15PWT	15	21.00	25.50	23.10
ZH1.5-16PWT	16	22.50	27.00	24.60
ZH1.5-17PWT	17	24.00	28.50	26.10
ZH1.5-18PWT	18	25.50	30.00	27.60
ZH1.5-19PWT	19	27.00	31.50	29.10
ZH1.5-20PWT	20	28.50	33.00	30.60



PCB LAYOUT
TOL.: ±0.05

序号	名称	数量
1	基座	1
2	接触针	n
3	焊片	2

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: ZH-SMT-AW针座	
DECIMALS:	ANGLES:	PAR	ZH1.5-XPWT
X.:±0.30	X':±5°	DWN	Lucas
X.X:±0.25	X.X':±3°	CHKD	Ethan
X.XX:±0.20	X.XX':±1°	APVD	Jacob
CUSTOMER COPY		SCALE 1:1	UNIT:MM
		SIZE:A4	SHEET:1F1
			REV:A