

REV	ECN No.	DATE	REMARK
A	NEW	2021.01.02	NEW RELEASE











TABLE: 						
NO	PART	Q'TY	Material			
1	SHELL	1	Stainless Steel SUS304 T=0.30mm, NI 30u" MIN PLATED			
2	EMI Plate	1	Stainless Steel SUS301 T=0.10mm,NI 30u" MIN PLATED			
3	Mid Plate	1	Stainless Steel SUS301 T=0.15mm, Matte Tin plated 50u"min on solder area;Nickel 50u"min underplating over all.			
4	CONTACT	24	COPPER STEEL C18400, Au plated on contact area GF Plated on solder area;Nickel 50u"min underplating over all.			
5	HOUSING	1	LCP BLACK UL94 V-0			
GENERAL TOLERANCES (UNLESS SPECIFIED)		DRAWN BY: Date: HuangXiaoHao 2023.09.25		 深圳市中科兴达科技有限公司 Shenzhen Zhongke Xingda Technological Co.,Ltd. USB Type-C MID-MOUNT SINK1.0mm DUAL ROW SMT, CH=0.58mm PART NO. DWG NO. CF259-24LB12R-02 CF259-24-02		
X.XXX	±0.10	CHECKED BY: Date: liuzongliang 2023.09.25				
X.XX	±0.25					
X.X	±0.30	APPROVED BY: Date:				
ANGULAR	±3°	Jacky	2023.09.25			
THIRD ANGLE PROJECTION		UNT	SCALE	DRAWING	SHEET NO.	REV.
		mm	1:1	A4	1 OF 3	A

