







说明:

- 1.产品表面清洁,无锈蚀、氧化、裂纹、缺芯、毛刺、及其它机械损伤;
- 2.塑胶材料:LCP UL94V-0,颜色:本色;
- 3.焊片:黄铜,镍底30u"Min.,镀锡50u"Min.;
- 4.接触针:黄铜,镍底30u"Min.,镀锡50u"Min.;
- 5.满足灼热丝温度850度.
- 6.工作温度-40~+85°C
- 7.额定电流:3A AC/DC
- 8.额定电压:250V AC/DC
- 9.接触阻抗:10mΩ Max.
- 10.绝缘阻抗:1000MΩ Min.
- 11.耐电压:1000V AC FOR 1 MINUTE



P/N	PIN	DIM A	DIM B	DIM C
XH2.54-2PWT	2	2.50	9.90	5.90
XH2.54-3PWT	3	5.00	12.40	8.40
XH2.54-4PWT	4	7.50	14.90	10.90
XH2.54-5PWT	5	10.00	17.40	13.40
XH2.54-6PWT	6	12.50	19.90	15.90
XH2.54-7PWT	7	15.00	22.40	18.40
XH2.54-8PWT	8	17.50	24.90	20.90
XH2.54-9PWT	9	20.00	27.40	23.40
XH2.54-10PWT	10	22.50	29.90	25.90
XH2.54-11PWT	11	25.00	32.40	28.40
XH2.54-12PWT	12	27.50	34.90	30.90
XH2.54-13PWT	13	30.00	37.40	33.40
XH2.54-14PWT	14	32.50	39.90	35.90
XH2.54-15PWT	15	35.00	42.40	38.40
XH2.54-16PWT	16	37.50	44.90	40.90
XH2.54-17PWT	17	40.00	47.40	43.40
XH2.54-18PWT	18	42.50	49.90	45.90
XH2.54-19PWT	19	45.00	52.40	48.40
XH2.54-20PWT	20	47.50	54.90	50.90

PCB LAYOUT
TOL.: ±0.05

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: TJC3-SMT-AW针座
DECIMALS:	ANGLES:		PAR XH2.54-XPWT
X.:±0.30	X':±5°		DWN Lucas
X.X:±0.25	X.X':±3°		CHKD Ethan
X.XX:±0.20	X.XX':±1°		APVD Jacob
CUSTOMER COPY		SCALE:1:1	UNIT:MM
		SIZE:A4	SHEET:1F1
			REV:A