








序号	名称	数量
1	基座	1
2	阳接触针	n
3	焊片	2



P/N	PIN	DIM A	DIM B	DIM C
HY2.0-2PLT	2	2.00	8.00	4.80
HY2.0-3PLT	3	4.00	10.00	6.80
HY2.0-4PLT	4	6.00	12.00	8.80
HY2.0-5PLT	5	8.00	14.00	10.80
HY2.0-6PLT	6	10.00	16.00	12.80
HY2.0-7PLT	7	12.00	18.00	14.80
HY2.0-8PLT	8	14.00	20.00	16.80
HY2.0-9PLT	9	16.00	22.00	18.80
HY2.0-10PLT	10	18.00	24.00	20.80
HY2.0-11PLT	11	20.00	26.00	22.80
HY2.0-12PLT	12	22.00	28.00	24.80
HY2.0-13PLT	13	24.00	30.00	26.80
HY2.0-14PLT	14	26.00	32.00	28.80
HY2.0-15PLT	15	28.00	34.00	30.80
HY2.0-16PLT	16	30.00	36.00	32.80
HY2.0-17PLT	17	32.00	38.00	34.80
HY2.0-18PLT	18	34.00	40.00	36.80
HY2.0-19PLT	19	36.00	42.00	38.80
HY2.0-20PLT	20	38.00	44.00	40.80



PCB LAYOUT



说明:

- 1.产品表面清洁,无锈蚀、氧化、裂纹、缺芯、毛刺、及其它机械损伤;
- 2.塑胶材料:LCP UL94V-0,颜色:本色;
- 3.焊片:黄铜,镍底30u"Min.,镀锡50u"Min.;
- 4.接触针:黄铜,镍底30u"Min.,镀锡50u"Min.;
- 5.满足灼热丝温度850度.
- 6.工作温度-40~+85°C
- 7.额定电流:2A AC/DC
- 8.额定电压:100V AC/DC
- 9.接触阻抗:10mΩ Max.
- 10.绝缘阻抗:1000MΩ Min.
- 11.耐电压:800V AC FOR 1 MINUTE

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: PHB-SMT-A		
		PAR	HY2.0-XPLT	
DECIMALS:	ANGLES:	DWN	Lucas	
X.:±0.30	X':±5°	CHKD	Ethan	
X.X:±0.25	X.X':±3°	APVD	Jacob	
X.XX:±0.20	X.XX':±1°	SCALE:1:1	UNIT:MM	
CUSTOMER COPY		SIZE:A4	SHEET:1F1	REV:A