







NO.	SPEC	Q'TY
1	HOUSING	1
2	TERMINAL	n
3	FITTING-NAIL	2
4	COVER	1




说明:

- 1.产品表面清洁,无锈蚀、氧化、裂纹、缺芯、毛刺、及其它机械损伤;
- 2.塑胶材料:LCP UL94V-0,颜色:本色;
- 3.焊片:黄铜,镀底30u"Min.,镀锡50u"Min.;
- 4.接触针:黄铜,镀底30u"Min.,镀锡50u"Min.;
- 5.满足灼热丝温度850度.
- 6.工作温度-40~+85°C
- 7.额定电流:1A AC/DC
- 8.额定电压:125V AC/DC
- 9.接触阻抗:20mΩ Max.
- 10.绝缘阻抗:500MΩ Min.
- 11.耐电压:250V AC FOR 1 MINUTE



P/N	PIN	DIM A	DIM B	DIM C
MX1.25-2PLT	2	1.25	7.25	3.05
MX1.25-3PLT	3	2.50	8.50	4.30
MX1.25-4PLT	4	3.75	9.75	5.55
MX1.25-5PLT	5	5.00	11.00	6.80
MX1.25-6PLT	6	6.25	12.25	8.05
MX1.25-7PLT	7	7.50	13.50	9.30
MX1.25-8PLT	8	8.75	14.75	10.55
MX1.25-9PLT	9	10.00	16.00	11.80
MX1.25-10PLT	10	11.25	17.25	13.05
MX1.25-11PLT	11	12.50	18.50	14.30
MX1.25-12PLT	12	13.75	19.75	15.55
MX1.25-13PLT	13	15.00	21.00	16.80
MX1.25-14PLT	14	16.25	22.25	18.05
MX1.25-15PLT	15	17.50	23.50	19.30
MX1.25-16PLT	16	18.75	24.75	20.55
MX1.25-17PLT	17	20.00	26.00	21.80
MX1.25-18PLT	18	21.25	27.25	23.05
MX1.25-19PLT	19	22.50	28.50	24.30
MX1.25-20PLT	20	23.75	29.75	25.55

RECOMMEND PCB LAYOUT
TOLERANCE:±0.05

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES				
DECIMALS:	ANGLES:	TITLE: 1.25-NP立贴闸口加蓋 卷装,壳锡,LCP		
X.:±0.30	X':±5°	PAR	MX1.25-XPLT	
X.X:±0.25	X.X':±3°	DWN	Lucas	
X.XX:±0.20	X.XX':±1°	CHKD	Ethan	
		APVD	Jacob	
		SCALE:1:1	UNIT:MM	
		CUSTOMER COPY	SIZE:A4	SHEET:1F1
				REV:A