




RoHS

REV.	ECN NO.	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	新版发行			2025.09.23

- 技术要求:
- 1.打铜底0.5-1μm,镍1-2μm, 镀雾锡3-5μm。
 - 2.铆好后不得有松动现象。
 - 3.插脚尖部符合可焊性要求。
 - 4.螺纹需符合通止规/止针要求。
 - 5.螺纹扭矩：1.8Nm.
 - 6.额定电流：80A.

铆M5螺母

PCB LAYOUT

XFCN 兴飞连接器

>30.±0.4	X.°±
6-30±0.3	.X°±
0-6±0.2	.XX°±
ANGLES±1°	.XXX°±
UNITS:	mm
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN	

PART NO: TMK56141155-1150		XFCN 兴飞连接器			
TITLE: PCB SOLDERING TERMINAL		0769-82001899			
		www.xfconn.com			
		DWG NO: /			
APPD	Chen ZhiQiang	VIEW			
CHKD	Liu Wei				
DRAW	Chen HongJiang	SCALE	SHEET	REV	
DATE	2025.09.23	NONE	1/1	A1	

2	螺母		SPCC	1
1	插脚		H62 (Y2)	1
序号	名称	零件编号	材质	数量