

This document contains proprietary information and such information may not be disclosed to others for any purposes,
not used for sales/marketing/procurement purposes without written permission

REV	DESCRIPTION OF REVISION	ECN NO.	BY	DATE	APPROVED
A	Initial Release	—	H.wei	26/07/17	26/07/17

1 Electrical 电气性能

1.1 Impedance 特性阻抗: 78 Ω

1.2 Frequency 频率范围: DC~500MHz

2 Environmental&Mechanical 环境&机械性能

2.1 Temperature range 温度范围: -55℃~+125℃

2.2 RoHs Compliant 符合RoHs

2.3 Durability 寿命: >500 cycles (次)



3 Materials&Finish 材料&涂镀

3.1 Body 外壳: Brass, Suco-Plated 黄铜, 镀三元


3.2 Insulator 绝缘介质: Teflon 聚四氟乙烯

3.3 Contact Pin 中心导体: Brass, Gold Plated 黄铜, 镀金

3.4 Outer Contact 外导体: Brass, Gold Plated 黄铜, 镀金



Recommended Mounting Hole



Notes:

1.ALL SPECIFICATIONS ARE SUBJECT TO CHANGE NOTICE AT ANY TIME

2.CUSTOMER OUTLINE DRAWING FOR REFERENCE ONLY

DRAWN : H.wei 26/07/17
ENGINEER: L.yu 26/07/17
APPROVED : W.yi 26/07/17
TOLERANCES UNLESS OTHERWISE SPECIFIED X ±0.50 .X ±0.20 .XX ±0.10 ANGLES ±1°

TITLE:
RF Coaxial Connector
TRB Female Connector PCB Mount
PART NO: HL-TRB-KHD

			
 DIMENSION IN MILLIMETERS (mm)			
SIZE: A4	SCALE: N/A	SHEET: 1/1	REV: A