

8

7

6

5

4

3

2

1

REV.

ECN NO.

DESCRIPTION

DESIGN

APPROVAL

DATE

A1

NEW

新版发行

2025.09.23

RoHS

9.0

9.0

3.5

6.0

1.7

7.8

PCB LAYOUT

技术要求:

1.打铜底0.5-1μm,镍2-2.5μm, 镀雾锡3-5μm。

2.铆好后不得有松动现象。

3.插脚尖部符合可焊性要求。

4.螺纹需符合通止规/止针要求。

5.螺纹扭矩：1.2Nm.

6.额定电流：60A.

M4-6H

11.5

3.2

1.2

9.0

9.0

7.0

1.2

6.5

>30.±0.4

X.°±

6-30±0.3

.X°±

0-6±0.2

.XX°±

ANGLES±1°

.XXX°±

UNITS:

mm

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN

PART NO:

TT44090090-1150

TITLE:

PCB SOLDERING TERMINAL

APPD

Chen ZhiQiang

CHKD

Liu Wei

DRAW

Chen HongJiang

DATE

2025.09.23

XFCN 兴飞连接器

0769-82001899

www.xfconn.com

DWG NO:

/

VIEW

SCALE

SHEET

REV

1/1

A1

2

垫片

SPCC

1

1

插脚

H62 (Y2)

1


序号

名称

零件编号

材质

数量

>30.±0.4	X.°±	PART NO: TT40490090-1150		XFCN 兴飞连接器			
6-30±0.3	.X°±						
0-6±0.2	.XX°±	TITLE: PCB SOLDERING TERMINAL		0769-82001899			
ANGLES±1°	.XXX°±			www.xfconn.com			
UNITS:	mm	APPD Chen ZhiQiang CHKD Liu Wei DRAW Chen HongJiang DATE 2025.09.23		DWG NO: /			
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN				VIEW			
				SCALE	SHEET	REV	
				NONE	1/1	A1	