

NOTE

1.SPECIFICATIONS

WITHSTANDING VOLTAGE: 500V AC

CURRENT RATING: 2AMP

INSULATION RESISTANCE: 1000MΩ MIN

CONTACT RESISTANCE: 20 mΩ MAX

TEMPERATURE RANGE: -55°C ~ +85°C

2.MATERIAL




HOUSING: THERMOPLASTIC UL94V-0

CONTACT: BRASS

3.FINISH: SEE TABLE

Table:

PART NAME	Q'TY	Material
CONTACT	1	C2680R-H,NI 80U"
HOUSING	1	PBT+30%GF,BLACK
CONTACT	1	C2680R-H,GOLD FLASH
CONTACT	1	C2680R-H,GOLD 15U"
CONTACT	1	C2680R-H,GOLD 30U"
CONTACT	1	C2680R-H,半金镍0.4U"



制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERL TOLERANCE		制图 DRAWING	ROSE			料号 PART NO.	ZX-254D-060-B	版本 REV.	A	
			.X±0.30	X.°±1°		审核 CHECK	LEO			品名 TITLE	2.54mm 开口短路帽	页次 SHEET	1/1
			.XX±0.20				JOHN			客户料号 CUTM.NO.			
			.XXX±0.10				核准 APPROVAL				兆星精密电子（深圳）有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.		
					单位 UNITS	MM	比例 SCALE	1:1					