




Table:

PART NAME	Q'TY	Material
CONTACT	1	C2680R-H,NI 80U"
HOUSING	1	PBT+30%GF,BLACK
CONTACT	1	C2680R-H,GOLD FLASH
CONTACT	1	C2680R-H,GOLD 15U"
CONTACT	1	C2680R-H,GOLD 30U"
CONTACT	1	C2680R-H,半金镍0.4U"

NOTE

1.SPECIFICATIONS

WITHSTANDING VOLTAGE: 500V AC

CURRENT RATING: 2AMP

INSULATION RESISTANCE: 1000MΩ MIN

CONTACT RESISTANCE: 20 mΩ MAX

TEMPERATURE RANGE: -55°C ~ +85°C

2.MATERIAL

HOUSING: THERMOPLASTIC UL94V-0

CONTACT: BRASS

3.FINISH: SEE TABLE

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERL TOLERANCE		制图 DRAWING	EMMA			料号 PART NO.	BX-254D-060-B		版本 REV.	A
			.X±0.30	X.°±1°	审核 CHECK	EVA			品名 TITLE	2.54mm 开口短路帽		页次 SHEET	1/1
			.XX±0.20		核准 APPROVAL	JADE			客户料号 CUTM.NO.				
			.XXX±0.10		单位 UNITS	MM	比例 SCALE	1:1	 Bossie (博锡)				