






NOTE:

Technical data:

Insulator body:PBT+15% G.F UL94-V0

Curent Rating:3 AMP

Insulator resistance:1000 Megohms min

Dielectric withstanding:AC/DC 500V.

Contact Resistance:25mΩ

Contactmaterial:Bronze.

plating:Gold or tin over nickel

Operating Temperature:-40°C to +105°C

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	ROSE			料号 PART NO.	ZX-200D-060-B	版本 REV.	A							
			.X±0.25	X.°±1°					审核 CHECK	LEO			品名 TITLE	MJ PH2.0 H:3.5	页次 SHEET	1/1			
			.XX±0.20						核准 APPROVAL				JOHN			客户料号 CUTM.NO.			
			.XXX±0.10						单位 UNITS							MM	比例 SCALE	1:1	 兆星精密电子（深圳）有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.