



SPECIFICATIONS**Mechanical****Plug Mating Force:** 4.50kgf (9.92Lb) max**Plug Unmating Force:** 1.00~4.00kgf (2.21~8.82Lb)**Durability:** 10000 Cycles**Electrical****Current Rating:** 0.50A min**Contact Resistance:** 30mΩ max. (Initial)

60mΩ max. (After life test)

Dielectric Withstanding Voltage: 500V AC RMS**Insulation Resistance:** Unmated plug: 100MΩ min at 500V DC
Mated plug: 10MΩ min at 500V DC**Physical****Housing:** Thermoplastic, UL 94V-0 rated**Contact:** Copper alloy**Plating:** See "ORDERING INFORMATION"**Operating Temperature:** -40°C to +85°C**DisplayPort Connector****3V Series****DisplayPort, R/A,
T/H Type****DRAWING****ORDERING INFORMATION**

PRODUCT NO.: 3VD1120*-H7AO-4H

Display port series

Product series

D=Standard type

Termination type

1=R/A T/H

Connector type

1=Receptacle

5. No. of Pos.

20=20 POS

Lead code

H=Halogen-free

Package code

4=Soft tray

Extension code

Contact Area Plating

3=30µ" Gold

7=15µ" Gold